

# **VALVE HEAD W9 TYPE B EPDM**



### ART. NO. 600047E

## **GENERAL**

The KEOFITT CLASSIC W9 Sampling Valve is the original and leading sterilizable sampling valve in the world. Used in all industries for decades. More than 320 standard valve configurations. Unique serial no. for each valve\*.

The sampling valve can be used for any process sampling for microbiological, chemical and/or physical analysis.



Cleaning/sterilizing: Between batches: Valve in open position: Cleanable by means of CIP using the detergent solution suitable for the actual process media. Between samples: Valve in its normal closed position: cleanable by CIP as "Between batches" or the valve may be sterilized by means of steam SIP or chemical SIP using a procedure appropriate to the actual circumstances. For further advice, please contact Keofitt. Not recommended for autoclave due to plastic parts.



Designed for sampling of liquids with a viscosity of up to approx. 1.000 cP containing no particles larger than Ø3 mm. Sampling of more viscous liquids is possible, only will it take longer (depending on process pressure).

# **FEATURES**



Installation: Threaded socket connection M22x1.5

Operation: Turn knob - no spring (opens counterclockwise) Membrane: EPDM (#600052)

# **CERTIFICATION\***

· EU EC 1935/2004 · EU EC 2023/2006 · DK No. 1248 10/2018 · 3-A Certificate · ATEX 2014/34/EU · PED 2014/68/EU · FDA CFR 21 §177.2600 · USP Class VI · Keofitt DoC

# **TECHNICAL DATA**

### Material (process contact)

• Membrane

EPDM, BLACK (#600052)

### Material (without process contact)

· Steel parts · Knob

AISI 303 (1.4305) / AISI 316L (1.4404) PA6 (Black)

### Membrane

 Article Certification\* EPDM, BLACK (#600052) · EU EC 1935/2004 · EU EC 2023/2006 · DK No. 1248 10/2018 · FDA CFR 21 §177.2600 · USP Class VI REACH · RoHS · ADI Free · Keofitt DoC

### **Pressure & Temperature**

<ul> <li>Pressure</li> </ul>	0 - 12 bar / 0 - 174 psi
<ul> <li>Temperature</li> </ul>	1-130°C/34-266°F
<ul> <li>Air supply</li> </ul>	- ,

### **Net Weight**

· kg/lbs

0.239 kg/0.527 lbs

### **Spareparts**


776041EPDM

PARTS W9 HEAD 600041E/42E/43E/47E



\*For further information and download please visit www.keofitt.dk

KEOFITT A/S reserves the right to change technical data without notice! Valid version of the data sheets is available on www.keofitt.dk.







# **KEOFITT CLASSIC W9 SAMPLING VALVE - BODIES**

	HOSE PIECE	T/5,, LISI-CIVINIE BODIEZ	THREAD ML6XL,5	T/5, MEIDING ENDS
TANK WELDING Ø28		30006	CONTRACT OF STORE	<b>B</b>
PIPE WELDING 1"	C C C C C C C C C C C C C C C C C C C	asonto	escore	Soots
WELDING BODIES PIPE WELDING NW25	O C C C C C C C C C C C C C C C C C C C	isandas ug	C C C C C C C C C C C C C C C C C C C	<sup>ISanbar</sup> 40
IN-LINE VERTICAL		Isanbas 40	15 an bas 40	<sup>JSanbar</sup> 40
IN-LINE HORIZONTAL		UN LOSTICE	UD LOD TORES	UD LEARES

# 

_						
	TREAD	M28015 B50031 B50031 DIN 11651 DN 10 B50040 B50040		escost Markets		
CONNECTION BODIES	CLAMP 3"		On request	JSan Las LO	JSanbas 40	
	CLAMP 2"			ON LEARES	UD LEARES	
	CLAMP 1" & 114"	Froose	85022 65022		Ju ledner	- 25 -
	MINI CLAMP	George Storage		ON LEARES	Du ledner	
	VARIVENT (968		Stota Stota	UN LEARES	un leanes	
	VARIVENT Ø50	C C C C C C C C C C C C C C C C C C C	OCOOSE	UL LOTION STATION	Isanbar 40	~ ~

🗣 🗣 🗣 🗣